

# 经济节能不锈钢外壳实验室专用箱式电阻马弗炉

产品名称	经济节能不锈钢外壳实验室专用箱式电阻马弗炉
公司名称	苏州热优贸易有限公司
价格	.00/个
规格参数	品牌:捷克LAC 型号:LE 产品别名:实验炉
公司地址	苏州工业园区和顺路1号博济生能科技园210室
联系电话	0512-87186613 13912619019

## 产品详情

品牌	捷克LAC	型号	LE
产品别名	实验炉	产品用途	适用于工业，医疗，科研，高校实验室等领域，各种材料的烧结，软化，预热，回火，退火等热处理工艺

laboratory furnaces le -economy line	
经济型马弗炉le	
application	用途
<p>le lab furnaces are suitable for testing technology where the exact distribution of temperature, the controlled increase and decrease of temperature, and controlled cooling are important, and where it is also desirable that the heating elements are not in the interior space with the samples. this especially applies to heating material for the heat treatment of metal, various tests of sintering, calcination, determination of the softening point or of material sintering, combusting samples, enamel firing etc.</p>	<p>用于所有种类的实验 用于一些技术测试， 空间时的冷却控制。 、煅烧、软化点的确定</p>
<p>the le's rust-resistant coating ensures the long life of the furnace. the heating spirals are placed in tubes of silica glass. this partially protects the spirals from corrosion by aggressive materials which can be released during use. a programmable controller and the master switch are located on the front side of the furnace.</p>	<p>主要结构描述</p> <ul style="list-style-type: none"> <li>- 优质不锈钢外壳，</li> <li>- 门由耐火材料填充、</li> <li>- 高温室由绝缘的耐火</li> </ul>
<p>included in the standard design:</p> <ul style="list-style-type: none"> <li>- manually opening of the door downwards</li> </ul>	

-ht60b controller

-heating elements in silica tubes

-slide valve for opening the supply of air

-airing chimney

accessories for additional charge:

-controller ht 40p

-exhaust ventilator with draft damper (for ht 40p controller)

-rs 232 or rs 485 interface for connection with pc

-电热丝被石英管包围

-门上加厚矿物纤维面

-烟囱被安装在炉子后

-加热石英管包埋在面

-门上装有安全开关

-采用单相电源

-冷风扇装备的熔炉

-k型热电偶被安装在

标准设备包括

- ht60b控制器

-手动向下开门

可选附件（需要另行

-电脑连接端口r 232/4

-排气风扇或者烟囱

-监控软件和温度循环

-气体保护装置

优点

-实现不锈

-吸引人的设计

-顶部绝缘材料(低功

-可编程的高精确度的

-固态继电器ssr (流畅

-完美的车间操作，保

可选型号：

类型	控制器	最高温度	容积	外部尺寸(wxhxd)
lac		° c	l	mm
le 05/11	ht40b	1100	5	470x330x455
le 09/11	ht40b	1100	9,4	490x370x515
le 15/11	ht40b	1100	14,4	550x370x565
le 05/11	ht60b	1100	5	470x330x455
le 09/11	ht60b	1100	9,4	490x370x515
le 15/11	ht60b	1100	14,4	550x370x565