

# 花生牛奶杀菌机 蛋白饮料生产线

|      |   |
|------|---|
| 产品名称 | 花生牛奶杀菌机 蛋白饮料生产线                             |
| 公司名称 | 上海长隆工业设备有限公司                                |
| 价格   | .00/台                                       |
| 规格参数 | 种类:蛋白饮料生产线<br>品牌:长隆<br>型号:1000L/H--20000L/H |
| 公司地址 | 上海市奉贤区南桥镇肖南路1555号                           |
| 联系电话 | 18918007988 13918733638                     |

## 产品详情

|      |                       |      |            |
|------|-----------------------|------|------------|
| 种类   | 蛋白饮料生产线               | 品牌   | 长隆         |
| 型号   | 1000L/H--20000L/H     | 产品用途 | 蛋白饮料的杀菌    |
| 外形尺寸 | 1800*1500*1500 ( mm ) | 净重   | 850 ( kg ) |
| 包装   | 木箱                    | 适用范围 | 其他         |
| 营销   | 新品                    |      |            |

有不详之处请来电详资13918733638（叶楠女士，市场部经理）

high temperature

sterilizer(htst)

高温杀菌机

高温杀菌机介绍

u产品介绍：具有高温、瞬时杀菌的特点。

u杀菌温度介于巴氏与超高温之间，一般适用于120 ，保温时间在10—15秒。

u生产能力：0.5—20t/h。

u控制方式：半自动控制、全自动控制（plc控制，触摸屏显示）。

product description: high temperature and instant sterilization etc features.

the sterilizing temperature is between pasteurization temperature and ultra-high temperature. in general, it is 120 .  
the heat preservation period is 10~15 seconds.

production capacity:0.5~20t/h

control methods:semi-automatin control, full-automatic control(plc control, touch screen display)

### 技术参数

| 名称name                            |          | br16-put-10b   | br16-put-20b   | br26-put-28b   | br26-put-45b   | br26-put-85b   | br56-put-150b  |
|-----------------------------------|----------|----------------|----------------|----------------|----------------|----------------|----------------|
| 生产能力capacity                      | t/h      | 1              | 2              | 3              | 5              | 10             | 20             |
| 换热面积heat exchanging area          | m2       | 10             | 20             | 28             | 45             | 85             | 150            |
| 物料进口温度material inlet temperature  |          | 5              | 5              | 5              | 5              | 5              | 5              |
| 物料出口温度material outlet temperature |          | 5              | 5              | 5              | 5              | 5              | 5              |
| 杀菌温度sterilizing temperature       |          | 120            | 120            | 120            | 120            | 120            | 120            |
| 保温时间heat preservation period      | s        | 15             | 15             | 15             | 15             | 15             | 15             |
| 冰水温度ice water temperature         |          | 1              | 1              | 1              | 1              | 1              | 1              |
| 冰水耗量ice water consumption         | multiple | 3              | 3              | 3              | 3              | 2              | 2              |
| 热水耗量hot water consumption         | multiple | 1.2            | 1.2            | 1.2            | 1.2            | 1.2            | 1.2            |
| 蒸汽压力steam pressure                | map      | 0.5            | 0.5            | 0.5            | 0.5            | 0.5            | 0.5            |
| 接口尺寸connecting size               | mm       | 38             | 38             | 38             | 51             | 50             | 63             |
| 外形尺寸outline dimension             | mm       | 1500*1500*1800 | 2000*2000*1800 | 2400*2000*2200 | 2800*2000*2200 | 3200*2000*2200 | 3500*2000*2200 |

