

# GEMU气动隔膜阀C60 12D77305A12 HPW/C60 8D 78205A12HPW

产品名称	GEMU气动隔膜阀C60 12D77305A12 HPW/C60 8D 78205A12HPW
公司名称	北京域能汇通科技有限公司
价格	3333.00/个
规格参数	品牌:盖米/GEMU 型号:GEMU C60 产地:德国
公司地址	北京市朝阳区立清路8号3-2205
联系电话	86-010-65911327-101 18614088757

## 产品详情

GEMU气动隔膜阀C60 12D77305A12 HPW/C60 8D 78205A12HPW

### 结构

外控式超纯两位两通隔膜阀CleanStar C60 HPW拥有全PFA阀体。所有接触介质的部件均采用PFA或PTFE (膜片) 材质。活塞执行器的外壳由PVDF材质制成。

冲程限制装置和可视指示器在该款阀门上属于标配 (1)。C60拥有坚固的集成一体式固定孔 (2)。

同时阀门可连接泄漏传感器 (3)。

扩孔接口的锁紧螺母 (4) 可选择PVDF、PFA和CPFA材质。执行器的锁紧螺母 (5) 可选择PVDF或ECTFE材质。

### 特点

特别适合高纯度介质

无金属 (控制方式3)

高流通能力

锁紧螺母/Flare接口兼容其他HP产品

于洁净室条件下制造

优点

最小污染

高流量规格

高K

v/Cv值

死区小

任意流动方向

也有T型阀提供，从而节省T型接头和所占空间

可选带ECTFE锁紧螺母 (5)的阀门

由此：

缩短设备冲洗时间

显著提高流通性 (高流量)

提高“平均故障间隔时间”(MTBF)

降低费用

VALVE COOLANT DIAPHRAGM GEMU 61015, D7 - 55-000-076 FOR MANUFACTURING OF SPECTACLE LENS

SPARE DIAPHRAGM TYPE 600 40M13 FOR GEMU VALVES(FOR CAPTIVE CONSUMPTION)

SPARE DIAPHRAGM TYPE 600 8M3A FOR GEMU VALVES(FOR CAPTIVE CONSUMPTION)

SPARE DIAPHRAGM TYPE 600 25M13 FOR GEMU VALVES(FOR CAPTIVE CONSUMPTION)

SPARE DIAPHRAGM TYPE 600 10M13 FOR GEMU VALVES(FOR CAPTIVE CONSUMPTION)

DIAPHRAGM VALVE - GEMU VALVE,534 20D 89051 1RS033 WITH 1434POSTIONER &REQUIRED ACCESSORIES

DIAPHRAGM VALVE - GEMU VALVE,534 25D 89051 1RS034 WITH 1434POSTIONER &REQUIRED ACCESSORIES

DIAPHRAGM VALVE - GEMU VALVE,312 65M 8 8 51 2RS0217 WITH 1436 POSTIONER &REQUIRED ACCESSORIES

VALVE - MANUAL DIAPHRAGM VALVE DN 15: GEMU

VALVE - PNE. DIAPHRAGM VALVE 1 GEMU

VALVE - PNE. DIAPHRAGM VALVE 1/2 GEMU

DIAPHRAGM VALVE MANUAL SIZE:DN25 SS316L,TC ENDS AS PER ASMEBPE FITTED WITH PTFE BACKED UP BY EPDM DIAPHRAGM, MAKE:GEMU

5075488- MANUAL L TYPE DIAPHRAGM VALVE, 2.5X10MM(M)-L-TYPE-PTFE-GEMU-SS-SS (PROJECT CODE-H-16063)(TAG NO:352.91 ML2VT1

5075322- MANUAL SAMPLING DIAPHRAGM VALVE-1/2 MSV-WOSIP-BW-EPDM-GEMU (PROJECT CODE: M-15042)(TAGNO.:D-BPT 01) (PR: 7000

5075492- PNEUMATIC ACTUATED L TYPE DIAPHRAGM VALVE, 2.5X1(A)-L-TYPE-PTFE-GEMU-ACT (PROJECT CODE-H-16063)(TAG NO:352.91

CV6D205-PNEU-DIAPHRAGM VALVE DN25 NO-GEMU DRAWING-ASPER INV.(1 NOS-EUR-316)

CV6D171-PNU-DIAPHRAGM VALVE -DN 40-NO-GEMU-DRAWING- ASPER INV (01 NOS- EUR-410)

CV6D070-PNU-DIAPHRAGM VALVE-DN40-GEMU-PTFE-DRAWING-ASPER INV.(1 NOS-EUR-398)

CV6D068-PNU-DIAPHRAGM VALVE -DN 15-GEMU-DRAWING- ASPER INV (30 NOS- EUR-132)

CV6D171-PNEU-DIAPHRAGM VALVE -DN40-NO-GEMU DRAWING-ASPER INV.(1 NOS-EUR-410)

5075487- MANUAL L TYPE DIAPHRAGM VALVE-2.5X1/2(M)-L TYPE-PTFE-GEMU-SS-SS (PROJECT CODE:H-16063)(TAGNO.)(PR.7000088163

5075487- MANUAL L TYPE DIAPHRAGM VALVE-2.5X1/2(M)-L TYPE-PTFE-GEMU-SS-SS (PROJECT CODE:H-16063)(TAGNO.352.91.ML2VT1-2

5075489- MANUAL L TYPE DIAPHRAGM VALVE-2.5X3/4(M)-L TYPE-PTFE-GEMU-SS-SS (PROJECT CODE:H-16063)(TAGNO.352.91.ML2VT1-2

5142512- MANUAL DIAPHRAGM VALVE-1/2 O.D. MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE: M-15042)(TAGNO.:T-PRV 03) (PR: 70

5075518- MANUAL T PATTERN DIAPHRAGM VALVE-2.5X8MM-T DV-PTFE-SS-SS-GEMU (PROJECT CODE:H-16063)(TAGNO.352.91.MS1VB1-230

5075518- MANUAL T PATTERN DIAPHRAGM VALVE-2.5X8MM-T DV-PTFE-SS-SS-GEMU (PROJECT CODE:H-16063)(TAGNO.352.91.MS1VB1-250

5075487- MANUAL L TYPE DIAPHRAGM VALVE-2.5X1/2(M)-L TYPE-PTFE-GEMU-SS-SS(PROJECT CODE:H-16063)(TAGNO.352.91.ML2VT1-24

5075518- MANUAL T PATTERN DIAPHRAGM VALVE-2.5X8MM-T DV-PTFE-SS-SS-GEMU (PROJECT CODE:H-16063)(TAGNO.LOOSE SUPPLY)(PR.

5075520- MANUAL T PATTERN DIAPHRAGM VALVE-3X8MM-T DV -PTFE-SS-SS-GEMU(PROJECT CODE:H-16063)(TAGNO.352.91.ML2VT1-2201)

GEMU CLAMPED DIAPHRAGM VALVE (EPDM+PTFE DOUBLE DIAPHRAGM),WITH STAINLESS STEEL HANDWHEEL : STAINLESS STEEL VALVE & PIPE

PTFE BACKED WITH EPDM DIAPHRAGM FOR GEMU VALVE 617 12D SIZE : DN12 ( 02 PCS )

214380622306 - GEMU ADV NO-SS316L PLAIN END EPDM-DN40 ACTUATED DIAPHRAGM VALVE TWO WAY

214200622307 - GEMU MDV SS316L PLAIN END-SS+PP+EPDM-DN50 MANUAL DIAPHRAGM VALVE TWO WAY MOC

214370622306 - GEMU ADV NC-SS316L PLAIN END EPDM-DN40 ACTUATED DIAPHRAGM VALVE TWO WAY

214380622307 - GEMU ADV NO-SS316L PLAIN END EPDM-DN50 ACTUATED DIAPHRAGM VALVE TWO WAY

GEMU PNEUM DIAPHRAGM VALVE(PARTS FOR SDI 2200 WATER ANALAYZER)

214200622304 - GEMU MDV SS316L PLAIN END-SS+PP+EPDM-DN25 MANUAL DIAPHRAGM VALVE TWO WAY MOC

5142515- MANUAL DIAPHRAGM VALVE- 1.5 O.D. MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16063) (TAG NO.POST TREATMENT)

5142514- MANUAL DIAPHRAGM VALVE- 1 O.D. MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16063) (TAG NO.POST TREATMENT) (P

5075485- MANUAL DIAPHRAGM VALVE-2.5-MDV-PTFE-BL-BW-GEMU-S-S (PROJECT CODE: H-16063)(TAGNO.:LOOSE SUPPLY) (PR: 1400020945

5073841- PNUMATIC ACTUATED DIAPHRAGM VALVE- 1BW ADV-EPDM-CAST-GEMU (PROJECT CODE: H-16034) (TAG NO.:) (PR:7000082603/25

5142514- MANUAL DIAPHRAGM VALVE-1O.D.MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16034) (TAG NO:) (PR:7000084571/ 10.

5142512- MANUAL DIAPHRAGM VALVE-1/2O.D.MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16034) (TAG NO:) (PR:7000084570/ 1

5073834- PNUMATIC ACTUATED DIAPHRAGM VALVE- 1 BW.ADV-PTFE-CAST-GEMU (PROJECT CODE:H-16063) (TAG NO.POST TREATMENT) (PR

5075482- MANUAL DIAPHRAGM VALVE-1-MDV-PTFE-BL-BW-GEMU-S-S (PROJECT CODE: H-16063)(TAGNO.:352.91.MD1VT1-2201) (PR: 140002

5075519- MANUAL T PATTERN DIAPHRAGM VALVE-2.5X1/2MM-T DV-PTFE-SS-SS-GEMU (PROJECT CODE:H-16063) (TAG NO.352.91.MS1VB

5073839- PNUMATIC ACTUATED DIAPHRAGM VALVE- 1/2BW ADV-EPDM-CAST-GEMU (PROJECT CODE: H-16034) (TAG NO.:) (PR:7000082602/

5142512- MANUAL DIAPHRAGM VALVE-1/2O.D.MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16034) (TAG NO:) (PR:7000082604/ 2

5142517- MANUAL DIAPHRAGM VALVE-2.5O.D.MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16034) (TAG NO:) (PR:7000084572/ 1

5142514- MANUAL DIAPHRAGM VALVE-1O.D.MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16034) (TAG NO:) (PR:7000088315/ 22.

5122743- ACTUATED DIAPHRAGM VALVE- 1/2 O.D. BW-ADV-PTFE-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H.16063) (TAG NO.:POST TREAT

5075493- MANUAL T PATTERN DIAPHRAGM VALVE-1X8MM)M)-T PATTERN-PTFE-GEMU-BT-ACT(PROJECT CODE:H-16063) (TAG NO.POST TREAT

5142513- MANUAL DIAPHRAGM VALVE-3/4O.D.MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16034) (TAG NO:) (PR:7000082605/ 2

5142502- MANUAL DIAPHRAGM VALVE-2 O.D.MDV-PTFE-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16063) (TAG NO.POST TREATMENT) (PR:

5075486- MANUAL DIAPHRAGM VALVE-3-MDV-PTFE-BL-BW-GEMU-S-S (PROJECT CODE: H-16063)(TAGNO.:LOOSE SUPPLY) (PR: 1400020945/1

5142520- MANUAL DIAPHRAGM VALVE-3/4O.D.MDV-EPDM-PL-PL-CAST-GEMU (PROJECT CODE:H-16002) (TAG NO:ANNEXURE) (PR:7000088334

5142514- MANUAL DIAPHRAGM VALVE-1O.D.MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16034) (TAG NO:) (PR:7000085393/ 20.

5142514- MANUAL DIAPHRAGM VALVE-1O.D.MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16034) (TAG NO:) (PR:7000082606/ 25.

5142512- MANUAL DIAPHRAGM VALVE- 1/2 O.D. MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16063) (TAG NO.POST TREATMENT)

5142498- MANUAL DIAPHRAGM VALVE- 1/2 O.D. MDV-EPDM-SS-PLASTIC-CAST-GEMU (PROJECT CODE:H-16063) (TAG NO.POST TREATMENT)

5074893-(VALVE SIZE40X15) 1.5 OD AUTO FLUSH BOTTOM DIAPHRAGM VALVE- 1.5 OD-AFBV-SAMP-EPDM-BL-GEMU (PROJECT CODE M-1600

VALVES AND PARTS THEREOF- DIAPHRAGM EPDM 50 NB PTFE BACK UPDIAPHARGM GOR GEMU ZDV VALVE SIZE : 50 X 50 X 15

CV6D171-PNEU.DIAPHRAGM VALVE-DN40-NO-GEMU DRAWING-ASPER INV.(2 NOS-EUR-410)

CV6D107-PNU.DIAPHRAGM VALVE-DN20-GEMU DRAWING-ASPER INV.(5 NOS-EUR-162)

CV6D107-PNU.DIAPHRAGM VALVE-DN20-GEMU DRAWING-ASPER INV.(1 NOS-EUR-162)

CV6D068-PNU-DIAPHRAGM-VALVE-DN15-GEMU-DRAWING-ASPER INV.(8 NOS-EUR-132)

CV6D205 PNEU DIAPHRAGM VALVE-GEMU-DN15-BW-0.6RA DRAWING-ASPER INV.(3 NOS-EUR-316)

CV6D068 PNU-DIAPHRAGM VALVE=DN15-GEMU DRAWING-ASPER INV.(5 NOS-EUR-132)

GEMU DIAPHRAGM VALVE PNEUMATIC OPERATED,NORMALLY CLOSE TYPE615 15D 1125211/N  
(PART OF SAND MIXTURE)(CAPTIVE CONUMPTION)

5122743- ACTUATED DIAPHRAGM VALVE, 1/2OD BW.ADV-PTFE-SS-PLASTIC-CAST-GEMU ( PROJECT  
CODE : M-16002 ) ( TAG NO : MV-01 )

5073137- SAMPLING VALVE WITH SIP PORT AND MANUAL DIAPHRAGM VALVE,1/2X1/2-SV-PTFE-BW-  
SS316L-GEMU ( PROJECT CODE : M-1600

GEMU MAKE PNEUMATIC OPERATED DIAPHRAGM VALVE

5122778- ACTUATED DIAPHRAGM VALVE,1.5OD BW.ADV-PTFE-SS-PLASTIC-CAST-GEMU (PROJECT  
CODE: M-16002 ) ( TAG NO: MV-04) (PR

5074866- MANUAL DIAPHRAGM VALVE,1 O.D.MDV-PTFE-PL-PL-CAST-GEMU (PROJECT  
CODE:M-16002) (TAG NO : MV-04)(PR :7000080326 /

5074866- MANUAL DIAPHRAGM VALVE, 1 O.D.MDV-PTFE-PL-PL-CAST-GEMU (PROJECT CODE  
:M-16002) (TAG NO: WFI-01) (PR:7000080432

5074247- MANUAL FLUSH BOTTOM DIAPHRAGM VALVE WITHOUT SIP VALVE, 1-MFBV-PTFE-BW-  
SS316L-GEMU (PROJECT CODE:M-16002) (TAG

5074247- MANUAL FLUSH BOTTOM DIAPHRAGM VALVE WITHOUT SIP VALVE 1-MFBV-PTFE-BW-  
SS316L-GEMU ( PROJECT CODE : M-16002 ) (

5122747- ACTUATED DIAPHRAGM VALVE, 1OD BW.ADV-PTFE-SS-PLASTIC-CAST- GEMU ( PROJECT  
CODE : M-16002 ) ( TAG NO : CIP DOCK

5122747- ACTUATED DIAPHRAGM VALVE 1OD BW.ADV-PTFE-SS-PLASTIC-CAST- GEMU ( PROJECT  
CODE : M-16002 ) ( TAG NO : MV-04 ) (

5142505- MANUAL DIAPHRAGM VALVE,1/2 O.D.MDV-PTFE-PL-PL-CAST-GEMU ( PROJECT CODE :  
M-16002 ) ( TAG NO : PIPING ) ( PR :

5122743 - ACTUATED DIAPHRAGM VALVE, 1/2OD BW.ADV-PTFE-SS-PLASTIC-CAST- GEMU ( PROJECT  
CODE : M-16002 ) ( TAG NO : MV-04

5122743- ACTUATED DIAPHRAGM VALVE, 1/2OD BW.ADV-PTFE-SS-PLASTIC-CAST-GEMU ( PROJECT

CODE : M-16002 ) ( TAG NO : MV-03 )

5073137- SAMPLING VALVE WITH SIP PORT AND MANUAL DIAPHRAGM VALVE 1/2X1/2-SV-PTFE-BW-SS316L-GEMU ( PROJECT CODE : M-1600

5148008-MANUAL DIAPHRAGM VALVE, 1/2 OD-MDV-EPDM-BL-GEMU-S-P ( PROJECT CODE : M-16010 ) ( TAG NO : ) ( PR : 7000081065 /

5074891- ACTUATED DIAPHRAGM VALVE, 1.5 OD-ADV-EPDM-BL-GEMU ( PROJECT CODE : M-16004 ) ( TAG NO : ) ( PR : 7000082927 /

5144934-ACTUATED DIAPHRAGM VALVE, 1 OD-ADV-EPDM-BL-GEMU ( PROJECT CODE : M-16004 ) ( TAG NO : ) ( PR : 7000083027 / 28.

5074866- MANUAL DIAPHRAGM VALVE,1 O.D.MDV-PTFE-PL-PL-CAST-GEMU(PROJECT CODE: M-16002) (TAG NO:DV-01) (PR:7000080424 / 0

5142505- MANUAL DIAPHRAGM VALVE, 1/2 O.D.MDV-PTFE-PL-PL-CAST-GEMU ( PROJECT CODE : M-16002 ) ( TAG NO : MV-04 ) ( PR :

5122743- ACTUATED DIAPHRAGM VALVE, 1/2OD BW.ADV-PTFE-SS-PLASTIC-CAST-GEMU ( PROJECT CODE : M-16002 ) ( TAG NO : CIP DOC

5073137-SAMPLING VALVE WITH SIP PORT AND MANUAL DIAPHRAGM VALVE, 1/2X1/2-SV-PTFE-BW-SS316L-GEMU( PROJECT CODE : M-16002

5073137- SAMPLING VALVE WITH SIP PORT AND MANUAL DIAPHRAGM VALVE1/2X1/2-SV-PTFE-BW-SS316L-GEMU ( PROJECT CODE : M-16002

5148011- MANUAL DIAPHRAGM VALVE, 1.5 OD-MDV-EPDM-BL-GEMU-S-P ( PROJECT CODE : M-16010 ) ( TAG NO : ) ( PR : 7000081070

5074891-ACTUATED DIAPHRAGM VALVE,1.5 OD-ADV-EPDM-BL-GEMU ( PROJECT CODE : M-16004 ) ( TAG NO : ) ( PR : 7000082926 / 28

5144934- ACTUATED DIAPHRAGM VALVE, 1 OD-ADV-EPDM-BL-GEMU ( PROJECT CODE : M-16004 ) ( TAG NO : ) ( PR : 7000083026 / 28

5144934-ACTUATED DIAPHRAGM VALVE, 1 OD-ADV-EPDM-BL-GEMU ( PROJECT CODE : M-16004 ) ( TAG NO : ) ( PR : 7000083029 / 28.